

7025 National Gold Tube

7025 National Gold Tube

Voltages applied to the tube:	Filament Voltage	12.6V
	Plate Voltage	250.0V
	Control Grid Voltage	-2.0V
Limits:	Max. Noise Level	100 μ Vrms
	Max. Microphonics	100 μ Vrms

A tube with a noise level greater than 100 μ Vrms would be rejected.

Microphonics are measured while the tube is being tapped. A tube with a microphonics measurement of 100 μ Vrms or less is accepted, while a tube with a measurement greater than 100 μ Vrms is rejected.

Output Current Scales For Matching

No.	No.
1. .840 mA - .912 mA	6. 1.201 mA - 1.272 mA
2. .913 mA - .984 mA	7. 1.273 mA - 1.344 mA
3. .985 mA - 1.056 mA	8. 1.345 mA - 1.416 mA
4. 1.057 mA - 1.128 mA	9. 1.417 mA - 1.488 mA
5. 1.129 mA - 1.200 mA	10. 1.489 mA - 1.560 mA