


Specification MAP/CV1050/Issue 6 Dated 24.1.49 To be read in conjunction with K1001.	SECURITY <table style="width: 100%; border: none;"> <tr> <td style="border: none; padding: 2px;"><u>Specification</u></td> <td style="border: none; padding: 2px;"><u>Valve</u></td> </tr> <tr> <td style="border: none; padding: 2px;">RESTRICTED</td> <td style="border: none; padding: 2px;">UNCLASSIFIED</td> </tr> </table>	<u>Specification</u>	<u>Valve</u>	RESTRICTED	UNCLASSIFIED																																																						
<u>Specification</u>	<u>Valve</u>																																																										
RESTRICTED	UNCLASSIFIED																																																										
→ Indicates a change																																																											
<table style="width: 100%; border: none;"> <tr> <td style="width: 60%;"><u>TYPE OF VALVE</u> -Triode</td> <td style="width: 40%; text-align: center;"><u>MARKING</u></td> </tr> <tr> <td><u>CATHODE</u> -Directly heated - oxide coated.</td> <td style="text-align: center;">See K.1001/4</td> </tr> <tr> <td><u>ENVELOPE</u> - Glass - unmetallised</td> <td style="text-align: center;"><u>PACKING</u></td> </tr> <tr> <td><u>PROTOTYPE</u> - HL2K</td> <td style="text-align: center;">See K.1005</td> </tr> <tr> <td></td> <td style="text-align: center;"><u>BASE</u></td> </tr> <tr> <td></td> <td style="text-align: center;">B4</td> </tr> </table>	<u>TYPE OF VALVE</u> -Triode	<u>MARKING</u>	<u>CATHODE</u> -Directly heated - oxide coated.	See K.1001/4	<u>ENVELOPE</u> - Glass - unmetallised	<u>PACKING</u>	<u>PROTOTYPE</u> - HL2K	See K.1005		<u>BASE</u>		B4																																															
<u>TYPE OF VALVE</u> -Triode	<u>MARKING</u>																																																										
<u>CATHODE</u> -Directly heated - oxide coated.	See K.1001/4																																																										
<u>ENVELOPE</u> - Glass - unmetallised	<u>PACKING</u>																																																										
<u>PROTOTYPE</u> - HL2K	See K.1005																																																										
	<u>BASE</u>																																																										
	B4																																																										
<table style="width: 100%; border: none;"> <tr> <td style="width: 40%;"><u>RATING</u></td> <td style="width: 10%;"></td> <td style="width: 10%; text-align: center;">Note</td> <td style="width: 30%;"></td> </tr> <tr> <td>Filament Voltage (V)</td> <td>2.0</td> <td></td> <td>1 Anode</td> </tr> <tr> <td>Filament Current (A)</td> <td>0.1</td> <td></td> <td>2 Grid</td> </tr> <tr> <td>Max. Anode Voltage (V)</td> <td>150</td> <td></td> <td>3 Filament negative</td> </tr> <tr> <td>Max. Anode Dissipation (W)</td> <td>1.0</td> <td></td> <td>4 Filament positive</td> </tr> <tr> <td>Mutual Conductance (mA/V)</td> <td>1.7</td> <td>A</td> <td></td> </tr> <tr> <td>Anode Impedance (Ω)</td> <td>16,500</td> <td>A</td> <td></td> </tr> <tr> <td>Amplification Factor</td> <td>26.5</td> <td>A</td> <td></td> </tr> <tr> <td>Max. Operating Frequency (Mc/s)</td> <td>20</td> <td></td> <td></td> </tr> </table>	<u>RATING</u>		Note		Filament Voltage (V)	2.0		1 Anode	Filament Current (A)	0.1		2 Grid	Max. Anode Voltage (V)	150		3 Filament negative	Max. Anode Dissipation (W)	1.0		4 Filament positive	Mutual Conductance (mA/V)	1.7	A		Anode Impedance (Ω)	16,500	A		Amplification Factor	26.5	A		Max. Operating Frequency (Mc/s)	20			<table style="width: 100%; border: none;"> <tr> <td colspan="4" style="text-align: center;"><u>DIMENSIONS</u></td> </tr> <tr> <td colspan="4" style="text-align: center;">See K.1001/AI/D1.</td> </tr> <tr> <td style="text-align: center;">Dimension</td> <td style="text-align: center;">Min.</td> <td colspan="2" style="text-align: center;">Max.</td> </tr> <tr> <td style="text-align: center;">A (mm)</td> <td style="text-align: center;">-</td> <td colspan="2" style="text-align: center;">90</td> </tr> <tr> <td style="text-align: center;">B (mm)</td> <td style="text-align: center;">-</td> <td colspan="2" style="text-align: center;">28</td> </tr> </table>			<u>DIMENSIONS</u>				See K.1001/AI/D1.				Dimension	Min.	Max.		A (mm)	-	90		B (mm)	-	28	
<u>RATING</u>		Note																																																									
Filament Voltage (V)	2.0		1 Anode																																																								
Filament Current (A)	0.1		2 Grid																																																								
Max. Anode Voltage (V)	150		3 Filament negative																																																								
Max. Anode Dissipation (W)	1.0		4 Filament positive																																																								
Mutual Conductance (mA/V)	1.7	A																																																									
Anode Impedance (Ω)	16,500	A																																																									
Amplification Factor	26.5	A																																																									
Max. Operating Frequency (Mc/s)	20																																																										
<u>DIMENSIONS</u>																																																											
See K.1001/AI/D1.																																																											
Dimension	Min.	Max.																																																									
A (mm)	-	90																																																									
B (mm)	-	28																																																									
<table style="width: 100%; border: none;"> <tr> <td style="width: 40%;"><u>CAPACITANCES (pF)</u></td> <td style="width: 10%;"></td> <td style="width: 10%;"></td> <td style="width: 30%;"></td> </tr> <tr> <td>Caf</td> <td>2.6</td> <td></td> <td></td> </tr> <tr> <td>Cgf</td> <td>3.5</td> <td></td> <td></td> </tr> <tr> <td>Cag</td> <td>3.7</td> <td></td> <td></td> </tr> </table>	<u>CAPACITANCES (pF)</u>				Caf	2.6			Cgf	3.5			Cag	3.7																																													
<u>CAPACITANCES (pF)</u>																																																											
Caf	2.6																																																										
Cgf	3.5																																																										
Cag	3.7																																																										
<u>NOTE</u> A: $V_a = 100, V_g = 0.$																																																											

To be performed in addition to those applicable in K.1001.

Test Conditions				Test	Limits		No. Tested
					Min.	Max.	
a	See K1001/AlII. Measured using adaptor type 35. Ref. 10A/13331			<u>CAPACITANCES (pF)</u>			
	Links to H.P.	Links to L.P.	Links to E.	1. Caf	-	4.0	6 per week
	1	3,4	2,5,6,7 8,9,10 TC.1, TC.2.				
	2	3,4	1,5,6,7 8,9,10 TC.1, TC.2.				
1	2	3,4,5,6 7,8,9, 10 TC1 TC.2.	3. Cag	-	5.5		
b	Vf	Va	Vg	If (A)	0.09	0.12	100% or S
	2.0	0	0				
c	2.0	100	0	Ia (mA)	2.3	4.1	100%
d	2.0	100	0	gm (mA/V)	1.35	2.00	100%
Peak grid swing + 0.5V.max.							
e	2.0	100	-2	Reverse Ig (μA)	-	1.0	100%
f	2.0	100	0	μ	23	30	100% or S
g	2.0 to 1.8	100	0	Ia drop (mA)	-	0.5	100%



SOURCE OF INFORMATION
HL2-OSRAM CATALOGUE
COPYRIGHT RESERVED